



www.lizardlickamusements.com

Wells-Gardner K7000 Series Monitor Cap Kit Checklist

Check off each cap you replace in the "X" column as you go!

X	Position	Capacitor Size	Notes
	C10	16v 33 μ f	
	C45	16v 470 μ f	
	C46	16v 470 μ f	
	C42	16v 1000 μ f	
	C20	25v 10 μ f	
	C21	25v 10 μ f	
	C11	25v 22 μ f	
	C13	25v 22 μ f	
	C23	25v 47 μ f	
	C48	35v 100 μ f	
	C40	35v 2200 μ f	
	C12	50v 1 μ f	
	C18	50v 1 μ f	
	C22	50v 1 μ f	
	C56	160v 22 μ f	
	C57	160v 47 μ f	
	C204	250v 4.7 μ f	*Neckboard

Notes:

We use Xicon Radial Electrolytic Capacitors in our cap kits, and they are polarized. Occasionally, we may substitute a higher voltage cap than indicated on this sheet or is already installed on your chassis. Higher rated caps are an acceptable replacement, never use a lower rated cap! The longer leg on the cap is positive. Negative is also indicated by a black band on the body of the cap, with a " - " sign.

***Replaces 4.7 μ f 160/200/250 cap found on some (but not all) neckboards.**